

## Technical Data Sheet

Article-No.: **710050**

Description:

**hourglass with clip  
metal casing**



DIMENSIONS				
length	width	height	diameter	lead time
68 mm	-	-	10 mm	15 s

PRODUCT DESCRIPTION							
<b>material</b>	<input type="checkbox"/> Polypropylene (PP)	<input type="checkbox"/> Polyethylene (PE)	<input type="checkbox"/> PP non woven	<input type="checkbox"/> PP non woven with PE coating	<input type="checkbox"/> paper	<input checked="" type="checkbox"/> aluminum	
<b>colour</b>	<input type="checkbox"/> blue [B]	<input type="checkbox"/> cedro [C]	<input type="checkbox"/> dark blue [DB]	<input type="checkbox"/> green [G]	<input type="checkbox"/> green opac [GO]	<input type="checkbox"/> purple [L]	<input type="checkbox"/> lightblue [LB]
	<input type="checkbox"/> Lime [LIME]	<input type="checkbox"/> Mix [MIX] black, cedro, purple, pink, lightblue	<input type="checkbox"/> orange [O]	<input type="checkbox"/> pink [P]	<input type="checkbox"/> red [R]	<input type="checkbox"/> rose [ROSE]	<input type="checkbox"/> black [SCH]
	<input type="checkbox"/> violett [V]	<input type="checkbox"/> white [W]	<input type="checkbox"/> wine red [WR]	<input type="checkbox"/> yellow [Y]	<input checked="" type="checkbox"/> silver	<input type="checkbox"/> natural	<input type="checkbox"/> bordeaux
<b>characteristics</b>	<input type="checkbox"/> single use	<input type="checkbox"/> single bladed	<input type="checkbox"/> 5 ply	<input type="checkbox"/> lint free	<input type="checkbox"/> 9 ply	<input type="checkbox"/> Filling quantity 2.000 ml	
<b>ingredients</b>	<input type="checkbox"/> 50% Urea (CAS 57-13-6)	<input type="checkbox"/> 50% water	<input type="checkbox"/> 70 % isopropyl alcohol				
<b>remark</b>							

REGULATORY AFFAIRS							
<b>PPE-Regulation (EU) 2016/425</b>	<input type="checkbox"/> Category I	<input type="checkbox"/> Category II	<input type="checkbox"/> Category III	<input checked="" type="checkbox"/> no PPE-article			
<b>#BEZUG!</b>	<input type="checkbox"/> Class I	<input type="checkbox"/> Class II	<input type="checkbox"/> Class III	<input type="checkbox"/> sterile	<input type="checkbox"/> measuring function	<input checked="" type="checkbox"/> no medical device	
<b>Food Contact (EG) 1935/2004</b>	<input type="checkbox"/> acidic foods	<input type="checkbox"/> aqueous foods	<input type="checkbox"/> fatty foods	<input type="checkbox"/> alcoholic foods	<input type="checkbox"/> dry foods	<input checked="" type="checkbox"/> not approved for food-contact	

## Technical Data Sheet

Article-No.: **710050**

Description:

**hourglass with clip  
metal casing**



LOGISTIC DATA SUBPACKING 1		
<b>general information</b>		
material	carton	
pieces per subpacking	10	
GTIN subpacking silver	4044941041803	
GTIN subpacking	-	
<b>measures &amp; size</b>		
length	111 mm	
width	76 mm	
height	15 mm	
<b>weights</b>		
<b>size</b>	<b>net weight</b>	<b>brut weight</b>
uni	90 g	125 g

LOGISTIC DATA OUTER PACKING		
<b>general information</b>		
material	carton	
subpackings per outer packing	10	
GTIN oute packing silver	4044941041780	
GTIN oute packing	-	
<b>measures &amp; size</b>		
length	470 mm	
width	240 mm	
height	465 mm	
<b>weights</b>		
<b>size</b>	<b>net weight</b>	<b>brut weight</b>
#BEZUG!	14.760 g	14.795 g

LOGISTIC DATA SUBPACKING 2		
<b>general information</b>		
material	carton	
boxes per outer packing	20	
GTIN oute packing silver	4044941041797	
GTIN oute packing	-	
<b>measures &amp; size</b>		
length	230 mm	
width	185 mm	
height	90 mm	
<b>weights</b>		
<b>size</b>	<b>net weight</b>	<b>brut weight</b>
uni	976 g	1.476 g

LOGISTIC DATA PALETTE		
<b>general information</b>		
kind of palette	euro-palette	
<b>measures &amp; size</b>		
cartons per layer	4	
layer per palette	4	
height of the palette	201 cm	
<b>weights</b>		
<b>size</b>	<b>net weight</b>	<b>brut weight</b>
uni	237 kg	262 kg

## Technical Data Sheet

Article-No.: **710050**

Description:

**hourglass with clip  
metal casing**



### WARNINGS AND SAFETY INFORMATION

<b>storage</b>	Store the item in its original packaging in a cool and dry place without additional weight load. Protect from heat, drops or strong impacts.
<b>use and control</b>	Before each use, ensure that the clip is securely attached to the desired position to prevent loss or falling. The product is tightly sealed. Forcibly opening it may cause injuries due to broken glass or leaking sand.
<b>cleaning instructions</b>	Clean with a dry or slightly damp cloth. Do not use aggressive cleaning agents.
<b>disposal</b>	The product must be disposed of in accordance with the disposal regulations of the local waste disposal company.
<b>warnings / safety information</b>	Forcibly opening it may cause injuries due to broken glass or leaking sand.

rev-no.: 2  
date: 31.01.2025

changes and errors excepted